# RHTemp125 L

Temperature and humidity data logger from -40°C to 125°C managed with Windows software and USB interface (DiskInterface HS, Universal Multibay). **Battery** is **user replaceable** and the data logger comes with a **Reference traceable cetificate** on several points.

Among the possible applications there are the drying processes monitoring, especially of pasta, of powders and grains storehouses, of extreme environments.



Applications Food & Beverages





Pharmaceutical

### **Main features**

- Small size
- Completely food grade
- User replaceable battery (software shows battery status)
- Accredia (NIST equivalent) traceable calibration certificate included
- Available extended calibration from 40°C (order extra calibration points)

#### Plus

- High accuracy and precision
- Printed reports compliant with health regulations and ISO (data are not editable in the software)

#### The system

The system is made up by:

- RHTemp temperature data logger
- DiskInterface HS or Universal Multibay
- HumiPressureDisk software or TS Manager software (compatible with the FDA 21 CFR Part 11 regulation)

#### Accessories

- HumiPressureDisk
- TS Manager
- DiskInterface HS
- Universal multibay
- Battery kit for RHTemp80 L and RHTemp125 L



Laboratories







## **Technical specifications**

Dimensions	46 h X 17 Ø mm - 18 Ø (mm) peek ring
Weight	36 g
Materials	Stainless steel AISI316L, PEEK
Temperature range	-40 °C ÷ +125 °C
Standard calibration points (temperature)	23/50°C
Extra calibration points (temperature)	Within the range -40 °C $\div$ +125 °C
Temperature resolution	0,015 °C
Temperature accuracy	± 0,2 °C (0 °C ÷ +60 °C) / ± 1,3 °C (-20 °C ÷ +80 °C) / ± 2,3 °C (-40 °C ÷ +125 °C) derates linearly
Humidity range	0% ÷ 100% RH (not condensing)
Standard calibration points (humidity)	30/50/70% @32°C ± 10°C
Extra calibration points (humidity)	Within the range 10% $\div$ 90% RH
Humidity reslution	0,02%
Humidity accuracy	± 1,8% RH (10% ÷ 80%) / ± 4% RH (80% ÷ 90%) @ 23°C ± 10°C
Humidity drift	1% ÷ 2% / year (depends on use conditions)
Memory (n. of acquisitions)	10.112
Battery life	+8.000.000 acquisitions at 1 second step continuously (calculated time @25°C. Battery life may be shorter if used in low temperatures)
Acquisition step	From 1 every second up, with 1 second steps
Protection degree	IP50
Software&Mobile App	HumiPressureDisk, TS Manager
Accessories	DiskInterface HS, Multibay universale



For more information, visit www.cik-solutions.com or contact us at info@cik-solutions.com

